



JK1E48S

## Technical characteristics

### Architecture

Fixing mode	surface-mounting
-------------	------------------

### Configuration

Number of modules	48
-------------------	----

### Compatibility

Suitable for lightning protection	No
-----------------------------------	----

### Dimensions

Insertion depth	110 mm
Depth of installed product	115 mm
Internal depth	107 mm
Height of installed product	655 mm
Width of installed product	405 mm
Width in division units	16
Thickness of sidewall material	1.2 mm

### Cover, door

Material thickness cover	1.2 mm
Identification od protection index	41
Interlockable	No
Door locking	with special tool
Transparent cover or door	No

### Materials

Colour	light grey
Material	Steel

### Installation, mounting

Suitable for outdoor use	No
--------------------------	----

### Connection

Number of conduit inlets	26
--------------------------	----

### Equipment

Number of rows	3
Quantity of rails	3
Extension possible	Yes

### Safety

IK protection code against mechanical impacts	IK05
Protection index IP	IP41
Protection class	isol.class I
RoHS conform	Yes