



JN2B00002S2

250A P'LBBOARD 2 WAY 125A OUTGOERS

Technical characteristics

Configuration

Number of modules	0
-------------------	---

Compatibility

Suitable for lightning protection	No
-----------------------------------	----

Dimensions

Insertion depth	163 mm
Depth of installed product	165 mm
Internal depth	155 mm
Height of installed product	700 mm
Width of installed product	615 mm
Thickness of sidewall material	1.5 mm

Cover, door

Material thickness cover	1.5 mm
Type of door closing	non keylock
Identification of protection index	41
Interlockable	No
Number of keylock of the door	0
Cover type	Closed (plain)
Door leave	single
Cover type	Cover
Transparent cover or door	No

Materials

Copper weight of the product	0.845 kg
Colour	light grey
Surface appearance	mat

Installation, mounting

Suitable for outdoor use	No
Suitable for ground mounting	No

Equipment

Quantity of rails	0
On/Off switch	No
Number of openings for flange plates	2
Extension possible	Yes

Standards

Approvals

BS EN 61439-2

Safety

IK protection code against mechanical impacts

IK05

Protection class

isol.class I

Glow wire test

according to IEC 61439-1

RoHS conform

Yes

Fire resistance

-