



JN2B00004S2

**250A P'LBBOARD 4 WAY 125A OUTGOERS**

**Technical characteristics**

**Configuration**

Number of modules	0
-------------------	---

**Compatibility**

Suitable for lightning protection	No
-----------------------------------	----

**Dimensions**

Insertion depth	163 mm
Depth of installed product	165 mm
Internal depth	155 mm
Height of installed product	775 mm
Width of installed product	615 mm
Thickness of sidewall material	1.5 mm

**Cover, door**

Material thickness cover	1.5 mm
Type of door closing	non keylock
Identification of protection index	41
Interlockable	No
Number of keylock of the door	0
Cover type	Closed (plain)
Door leave	single
Cover type	Cover
Transparent cover or door	No

**Materials**

Copper weight of the product	1.118 kg
Colour	light grey
Surface appearance	mat

**Installation, mounting**

Suitable for outdoor use	No
Suitable for ground mounting	No

**Equipment**

Quantity of rails	0
On/Off switch	No
Number of openings for flange plates	2
Extension possible	Yes

**Standards**

Approvals

BS EN 61439-2

**Safety**

IK protection code against mechanical impacts

IK05

Protection class

isol.class I

Glow wire test

according to IEC 61439-1

Fire resistance

-