



JN2B00008S2

## 250A Panel BOARD 8 WAY Surface

### Technical characteristics

#### Configuration

Number of modules	0
-------------------	---

#### Compatibility

Suitable for lightning protection	No
-----------------------------------	----

#### Dimensions

Insertion depth	163 mm
-----------------	--------

Depth of installed product	165 mm
----------------------------	--------

Internal depth	155 mm
----------------	--------

Height of installed product	925 mm
-----------------------------	--------

Width of installed product	615 mm
----------------------------	--------

Thickness of sidewall material	1.5 mm
--------------------------------	--------

#### Cover, door

Material thickness cover	1.5 mm
--------------------------	--------

Type of door closing	non keylock
----------------------	-------------

Identification of protection index	41
------------------------------------	----

Interlockable	No
---------------	----

Number of keylock of the door	0
-------------------------------	---

Cover type	Closed (plain)
------------	----------------

Door leave	single
------------	--------

Cover type	Cover
------------	-------

Transparent cover or door	No
---------------------------	----

#### Materials

Copper weight of the product	1.88 kg
------------------------------	---------

Colour	light grey
--------	------------

Surface appearance	matt
--------------------	------

#### Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Suitable for ground mounting	No
------------------------------	----

#### Equipment

Quantity of rails	0
-------------------	---

On/Off switch	No
---------------	----

Number of openings for flange plates	2
--------------------------------------	---

Extension possible	Yes
--------------------	-----

**Standards**

Approvals

BS EN 61439-2

**Safety**

IK protection code against mechanical impacts

IK05

Protection class

isol.class I

Glow wire test

according to IEC 61439-1

RoHS conform

Yes

Fire resistance

-