



KB363B

**Insulated busbar 3P 63A prong 10mm<sup>2</sup> 57M**

**Technical characteristics**

**Architecture**

Number of poles 3 P

**Configuration**

Number of modules 57

**Compatibility**

Intended for the compatible references Modular devices

**Main electrical features**

Rated operational voltage Ue 230 / 400 V

**Voltage**

Max operating voltage 400 V

Rated impulse withstand voltage 4 kV

**Electric current**

Rated current 63 A

**Dimensions**

Length 1000 mm

Pitch 17.8 mm

**Power supply**

Number of phases for the power supply 3-phase

**Materials**

Colour stone grey

**Installation, mounting**

Suitable to a device with an auxiliary No

**Connection**

Connection cross-sect. rigid cable 10mm<sup>2</sup>

Suitable for product with neutral busbar No

Connector type busbar prong

Type of connection with screw

**Equipment**

Number of appliances to build in 19

**Standards**

**Use conditions**

---

Insulated

Yes