



KB363B

Insulated busbar 3P 63A prong 10mm² 57M

Technical characteristics

Architecture

Number of poles 3 P

Configuration

Number of modules 57

Compatibility

Intended for the compatible references Modular devices

Main electrical features

Rated operational voltage Ue 230 / 400 V

Voltage

Max operating voltage 400 V

Rated impulse withstand voltage 4 kV

Electric current

Rated current 63 A

Dimensions

Length 1000 mm

Pitch 17.8 mm

Power supply

Number of phases for the power supply 3-phase

Installation, mounting

Suitable to a device with an auxiliary No

Connection

Connection cross-sect. rigid cable 10mm²

Suitable for product with neutral busbar No

Connector type busbar prong

Type of connection with screw

Equipment

Number of appliances to build in 19

Standards

European directive WEEE not concerned

Safety

REACH conform	Yes
RoHS conform	Yes
Use conditions	
Insulated	Yes