



KB363B

Insulated busbar 3P 63A prong 10mm² 57M

Technical characteristics

Architecture

Number of poles	3 P
-----------------	-----

Configuration

Number of modules	57
-------------------	----

Compatibility

Intended for the compatible references	Modular devices
--	-----------------

Main electrical features

Rated operational voltage Ue	230 / 400 V
------------------------------	-------------

Voltage

Max operating voltage	400 V
Rated impulse withstand voltage	4 kV

Electric current

Rated current	63 A
---------------	------

Dimensions

Length	1000 mm
Pitch	17.8 mm

Power supply

Number of phases for the power supply	3-phase
---------------------------------------	---------

Materials

Colour	stone grey
--------	------------

Installation, mounting

Suitable to a device with an auxiliary	No
--	----

Connection

Suitable for product with neutral busbar	No
--	----

Equipment

Number of appliances to build in	19
----------------------------------	----

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

REACH conform	Yes
---------------	-----

Subject to technical modifications

RoHS conform	Yes
--------------	-----

Use conditions

Insulated	Yes
-----------	-----