



KD463B

Insulated busbar 3P+N 63A fork 10mm² 57M

Technical characteristics

Architecture

Number of poles	4 P
Type of pole	3P+N

Voltage

Max operating voltage	400 V
-----------------------	-------

Electric current

Rated current	63 A
---------------	------

Dimensions

Length	1000 mm
Fixation distance in module steps	4

Connection

Connection cross-sect. rigid cable	10mm ²
Connector type	busbar fork
Type of connection	with screw

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

REACH conform	Yes
RoHS conform	Yes

Use conditions

Insulated	Yes
-----------	-----