



KDN163B

Insulated busbar 1P 63A fork 10mm² 57M

Technical characteristics

Architecture

Number of poles	1 P
Type of pole	1 P

Compatibility

Intended for the compatible references	Modular devices
----------------------------------------	-----------------

Main electrical features

Rated operational voltage Ue	415 V
------------------------------	-------

Voltage

Max operating voltage	230 V
-----------------------	-------

Electric current

Rated current	63 A
---------------	------

Dimensions

Length	1000 mm
Pitch	17.8 mm

Installation, mounting

Suitable to a device with an auxiliary	No
----------------------------------------	----

Connection

Connection cross-sect. rigid cable	10mm ²
Suitable for product with neutral busbar	No
Connector type	busbar fork
Type of connection	with screw / quick connect

Equipment

Number of appliances to build in	57
----------------------------------	----

Safety

REACH conform	No
RoHS conform	Yes

Use conditions

Insulated	Yes
-----------	-----