



KDN163B

## Insulated busbar 1P 63A fork 10mm<sup>2</sup> 57M

### Technical characteristics

#### Architecture

Number of poles	1 P
Type of pole	1 P

#### Compatibility

Intended for the compatible references	Modular devices
--	-----------------

#### Main electrical features

Rated operational voltage Ue	415 V
------------------------------	-------

#### Voltage

Max operating voltage	230 V
-----------------------	-------

#### Electric current

Rated current	63 A
---------------	------

#### Dimensions

Length	1000 mm
Pitch	17.8 mm

#### Installation, mounting

Suitable to a device with an auxiliary	No
--	----

#### Connection

Connection cross-sect. rigid cable	10mm <sup>2</sup>
Suitable for product with neutral busbar	No
Connector type	busbar fork
Type of connection	with screw / quick connect

#### Equipment

Number of appliances to build in	57
----------------------------------	----

#### Safety

REACH conform	No
RoHS conform	Yes

#### Use conditions

Insulated	Yes
-----------	-----