



KDN363A

Insulated busbar 3P 63A fork 10mm² 12M

Technical characteristics

Architecture

Number of poles	3 P
Type of pole	3 P

Compatibility

Intended for the compatible references	Modular devices
--	-----------------

Main electrical features

Rated operational voltage Ue	230 / 400 V
------------------------------	-------------

Voltage

Max operating voltage	400 V
-----------------------	-------

Electric current

Rated current	63 A
---------------	------

Dimensions

Length	210 mm
Pitch	17.8 mm

Installation, mounting

Suitable to a device with an auxiliary	No
--	----

Connection

Connection cross-sect. rigid cable	10mm ²
Suitable for product with neutral busbar	No
Connector type	busbar fork
Type of connection	with screw / quick connect

Equipment

Number of connections	12 C
-----------------------	------

Safety

REACH conform	No
RoHS conform	Yes

Use conditions

Insulated	Yes
-----------	-----