



KDN363A

**Insulated busbar 3P 63A fork 10mm<sup>2</sup> 12M**

**Technical characteristics**

**Architecture**

Number of poles	3 P
Type of pole	3 P

**Compatibility**

Intended for the compatible references	Modular devices
--	-----------------

**Main electrical features**

Rated operational voltage Ue	230 / 400 V
------------------------------	-------------

**Voltage**

Max operating voltage	400 V
-----------------------	-------

**Electric current**

Rated current	63 A
---------------	------

**Dimensions**

Length	210 mm
Pitch	17.8 mm

**Materials**

Colour	stone grey
--------	------------

**Installation, mounting**

Suitable to a device with an auxiliary	No
--	----

**Connection**

Suitable for product with neutral busbar	No
--	----

**Equipment**

Number of connections	12 C
-----------------------	------

**Standards**

European directive WEEE	concerned
-------------------------	-----------

**Use conditions**

Insulated	Yes
-----------	-----