



KDN380B

**Insulated busbar 3P 80A fork 16mm<sup>2</sup> 57M**

**Technical characteristics**

**Architecture**

Number of poles	3 P
Type of pole	3 P

**Compatibility**

Intended for the compatible references	Modular devices
--	-----------------

**Main electrical features**

Rated operational voltage Ue	230 / 400 V
------------------------------	-------------

**Voltage**

Max operating voltage	400 V
-----------------------	-------

**Electric current**

Rated current	80 A
---------------	------

**Dimensions**

Length	1000 mm
Pitch	17.8 mm

**Installation, mounting**

Suitable to a device with an auxiliary	No
--	----

**Connection**

Connection cross-sect. rigid cable	16mm <sup>2</sup>
Suitable for product with neutral busbar	No
Connector type	busbar fork
Type of connection	with screw / quick connect

**Equipment**

Number of connections	57 C
-----------------------	------

**Safety**

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

**Use conditions**

Insulated	Yes
-----------	-----