



KDN451D

Insulated busbar 3x(P+N) 80A fork 16mm² 12M

Technical characteristics

Architecture

Number of poles 4 P

Connectivity

Connector width 11.5 mm

Main electrical features

Rated operational voltage Ue 230 / 400 V

Voltage

Max operating voltage 400 V

Electric current

Rated current 80 A

Dimensions

Length 215 mm

Pitch 17.8 mm

Materials

Colour stone grey

Installation, mounting

Mounting way horizontal

Suitable to a device with an auxiliary No

Connection

Connection cross-sect. rigid cable 16mm²

Suitable for product with neutral busbar Yes

Cable

Conductor Size 16 mm²

Equipment

Number of connections 12 C

Number of appliances to build in 3

Standards

European directive WEEE concerned

Use conditions

Operating temperature -25...55 °C

Storage/transport temperature

-40...75 °C

Insulated

Yes