



KDN451D

Insulated busbar 3x(P+N) 80A fork 16mm² 12M

Technical characteristics

Architecture

Number of poles	4 P
Type of pole	3P+N

Connectivity

Connector width	11.5 mm
-----------------	---------

Main electrical features

Rated operational voltage Ue	230 / 400 V
------------------------------	-------------

Voltage

Max operating voltage	400 V
-----------------------	-------

Electric current

Rated current	80 A
---------------	------

Dimensions

Length	215 mm
Pitch	17.8 mm

Installation, mounting

Mounting way	horizontal
Suitable to a device with an auxiliary	No

Connection

Connection cross-sect. rigid cable	16mm ²
Suitable for product with neutral busbar	Yes
Connector type	busbar fork
Type of connection	with screw / quick connect

Cable

Conductor Size	16 mm ²
----------------	--------------------

Equipment

Number of connections	12 C
Number of appliances to build in	3

Safety

REACH conform	No
RoHS conform	Yes
Halogen free	No

Use conditions

Operating temperature	-25...55 °C
Storage/transport temperature	-40...75 °C
Insulated	Yes
