



Insulated busbar 4P 80A fork 16mm² 56M

Technical characteristics

Architecture	
Number of poles	4 P
Type of pole	4 P
Main electrical features	
Rated operational voltage Ue	230 / 400 V
Voltage	
Max operating voltage	400 V
Electric current	
Rated current	80 A
Dimensions	
Length	1000 mm
Pitch	17.8 mm
Installation, mounting	
Suitable to a device with an auxiliary	No
Connection	
Connection cross-sect. rigid cable	16mm²
Suitable for product with neutral busbar	Yes
Connector type	busbar fork
Type of connection	with screw / quick connect
Equipment	
Number of appliances to build in	14
Safety	
REACH conform	Yes
RoHS conform	Yes
Use conditions	
Insulated	Yes

KDN480B