



KM11N

**Brass terminal, 5x10mm<sup>2</sup> 5x16mm<sup>2</sup>,with mounting base, Color: blue**

**Technical characteristics**

**Architecture**

|                 |                        |
|-----------------|------------------------|
| Number of poles | 1 P                    |
| Fixing mode     | Clamping and screwable |

**Electric current**

|               |      |
|---------------|------|
| Rated current | 60 A |
|---------------|------|

**Dimensions**

|                            |       |
|----------------------------|-------|
| Length                     | 73 mm |
| Width of installed product | 5 mm  |

**Settings**

|               |                  |
|---------------|------------------|
| terminal type | Brass terminal N |
|---------------|------------------|

**Equipment**

|                   |    |
|-------------------|----|
| Number of outputs | 10 |
| Number of inputs  | 1  |

**Standards**

|                         |           |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

**Safety**

|               |     |
|---------------|-----|
| REACH conform | Yes |
| RoHS conform  | Yes |
| Halogen free  | No  |