



LF302M

**Cylindrical fuse-links for industrial applications 10x38mm aM 2A 500V AC 120kA**

**Technical characteristics**

**Functions**

Release characteristic fuses Time-lag

**Main electrical features**

Rated short circuit breaking capacity  $I_{cn}$  AC according IEC60898-1 120 kA

Rated operational voltage  $U_e$  500 V

Type of supply voltage AC

**Electric current**

Rated current 2 A

Rated ultimate short-circuit breaking capacity  $I_{cu}$  AC IEC 60947-2 120 kA

**Frequency**

Frequency 50 to 60 Hz

**Power**

Total power loss under  $I_N$  0.18 W

**Standards**

European directive WEEE concerned