



LF332G

Cylindrical fuse-links for industrial applications 10x38mm gG 32A 400V AC 120kA

Technical characteristics

Functions

Release characteristic fuses Time-lag

Main electrical features

Rated short circuit breaking capacity I_{cn} AC according IEC60898-1 120 kA

Rated operational voltage U_e 400 V

Type of supply voltage AC

Electric current

Rated current 32 A

Rated ultimate short-circuit breaking capacity I_{cu} AC IEC 60947-2 120 kA

Fuse

CharactFuse gG

Fuse Size 10.3 x 38

Frequency

Frequency 50 to 60 Hz

Power

Total power loss under I_N 2.9 W

Safety

REACH conform Yes

RoHS conform Yes

Halogen free Yes