



LF402G

Industrial fuse-links 14x51 gG 2A

Technical characteristics

Functions

Release characteristic fuses	Fast (F)
------------------------------	----------

Main electrical features

Rated short circuit breaking capacity Icn AC according IEC60898-1	120 kA
Rated operational voltage Ue	690 V
Type of supply voltage	AC

Electric current

Rated current	2 A
Rated ultimate short-circuit breaking capacity Icu AC IEC 60947-2	80 kA

Frequency

Frequency	50 to 60 Hz
-----------	-------------

Power

Total power loss under IN	0.9 W
---------------------------	-------

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes