



LF410G

## Industrial fuse-links 14x51 gG 10A

### Technical characteristics

#### Functions

Release characteristic fuses	Fast (F)
------------------------------	----------

#### Main electrical features

Rated short circuit breaking capacity $I_{cn}$ AC according IEC60898-1	80 kA
Rated operational voltage $U_e$	690 V
Type of supply voltage	AC

#### Electric current

Rated current	10 A
Rated ultimate short-circuit breaking capacity $I_{cu}$ AC IEC 60947-2	80 kA

#### Frequency

Frequency	50 to 60 Hz
-----------	-------------

#### Power

Total power loss under $I_N$	1.3 W
------------------------------	-------

#### Standards

European directive WEEE	concerned
-------------------------	-----------

#### Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes