



LF412M

Industrial fuse-links 14x51 aM 12A

Technical characteristics

Functions

Release characteristic fuses Time-lag

Main electrical features

Rated short circuit breaking capacity I_{cn} AC according IEC60898-1 80 kA

Rated operational voltage U_e 690 V

Type of supply voltage AC

Electric current

Rated current 12 A

Rated ultimate short-circuit breaking capacity I_{cu} AC IEC 60947-2 80 kA

Fuse

CharactFuse gG ; aM

Fuse Size 14 x 51

Frequency

Frequency 50 to 60 Hz

Power

Total power loss under I_N 0.88 W

Standards

European directive WEEE concerned