



LF425M

Industrial fuse-links 14x51 aM 25A

Technical characteristics

Functions

Release characteristic fuses	Time-lag
------------------------------	----------

Main electrical features

Rated short circuit breaking capacity I_{cn} AC according IEC60898-1	80 kA
Rated operational voltage U_e	690 V
Type of supply voltage	AC

Electric current

Rated current	25 A
Rated ultimate short-circuit breaking capacity I_{cu} AC IEC 60947-2	80 kA

Fuse

CharactFuse	gG ; aM
Fuse Size	14 x 51

Frequency

Frequency	50 to 60 Hz
-----------	-------------

Power

Total power loss under IN	1.46 W
---------------------------	--------

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes