



LF432G

### Industrial fuse-links 14x51 gG 32A

#### Technical characteristics

##### Functions

Release characteristic fuses	Fast (F)
------------------------------	----------

##### Main electrical features

Rated short circuit breaking capacity $I_{cn}$ AC according IEC60898-1	120 kA
--	--------

Rated operational voltage $U_e$	500 V
---------------------------------	-------

Type of supply voltage	AC
------------------------	----

##### Electric current

Rated current	32 A
---------------	------

Rated ultimate short-circuit breaking capacity $I_{cu}$ AC IEC 60947-2	120 kA
--	--------

##### Fuse

CharactFuse	gG
-------------	----

Fuse Size	14 x 51
-----------	---------

##### Frequency

Frequency	50 to 60 Hz
-----------	-------------

##### Power

Total power loss under $I_N$	3.5 W
------------------------------	-------

##### Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	Yes
--------------	-----