



LF432G

**Industrial fuse-links 14x51 gG 32A**

**Technical characteristics**

**Functions**

Release characteristic fuses	Fast (F)
------------------------------	----------

**Main electrical features**

Rated short circuit breaking capacity I <sub>cn</sub> AC according IEC60898-1	120 kA
Rated operational voltage U <sub>e</sub>	500 V
Type of supply voltage	AC

**Electric current**

Rated current	32 A
Rated ultimate short-circuit breaking capacity I <sub>cu</sub> AC IEC 60947-2	120 kA

**Fuse**

CharactFuse	gG
Fuse Size	14 x 51

**Frequency**

Frequency	50 to 60 Hz
-----------	-------------

**Power**

Total power loss under I <sub>N</sub>	3.5 W
---------------------------------------	-------

**Standards**

European directive WEEE	concerned
-------------------------	-----------

**Safety**

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes