



LF450M

## Industrial fuse-links 14x51 aM 50A

### Technical characteristics

#### Functions

Release characteristic fuses	Time-lag
------------------------------	----------

#### Main electrical features

Rated short circuit breaking capacity $I_{cn}$ AC according IEC60898-1	120 kA
Rated operational voltage $U_e$	400 V
Type of supply voltage	AC

#### Electric current

Rated current	50 A
Rated ultimate short-circuit breaking capacity $I_{cu}$ AC IEC 60947-2	120 kA

#### Fuse

CharactFuse	gG ; aM
Fuse Size	14 x 51

#### Frequency

Frequency	50 to 60 Hz
-----------	-------------

#### Power

Total power loss under $I_N$	2.9 W
------------------------------	-------

#### Standards

European directive WEEE	concerned
-------------------------	-----------

#### Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes