



LF599G

Cylindrical fuse-links for industrial applications 22x58mm gG 125A 500V AC 120kA

Technical characteristics

Functions

Release characteristic fuses	Time-lag
------------------------------	----------

Main electrical features

Rated short circuit breaking capacity Icn AC according IEC60898-1	120 kA
Rated operational voltage Ue	500 V
Type of supply voltage	AC

Electric current

Rated current	125 A
Rated ultimate short-circuit breaking capacity Icu AC IEC 60947-2	120 kA

Frequency

Frequency	50 to 60 Hz
-----------	-------------

Power

Total power loss under IN	11.4 W
---------------------------	--------

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes