



LR602

Fuse carrier 2P 50A 690V L51 3M

Technical characteristics

Architecture

Number of poles	2 P
Type of pole	2 P

Configuration

Number of modules	3
-------------------	---

Electric current

Rated current	50 A
---------------	------

Fuse

CharactFuse	gG ; aM
-------------	---------

Dimensions

Depth of installed product	93 mm
Height of installed product	107 mm
Width of installed product	52.5 mm

Power

Total power loss under IN	12.5 W
---------------------------	--------

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes

Use conditions

Operating temperature	-5...40 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	3
Storage/transport temperature	-25...80 °C