



LR704

**Fuse carrier 3P+N 125A 690V L58 8M**

**Technical characteristics**

**Architecture**

Number of poles	4 P
-----------------	-----

**Configuration**

Number of modules	8
-------------------	---

**Electric current**

Rated current	125 A
---------------	-------

**Dimensions**

Depth of installed product	96 mm
Height of installed product	125 mm
Width of installed product	140 mm

**Power**

Total power loss under IN	42 W
---------------------------	------

**Standards**

European directive WEEE	concerned
-------------------------	-----------

**Safety**

Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes

**Use conditions**

Operating temperature	-5...40 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	3
Storage/transport temperature	-25...80 °C