



RED611X



**IP20**

**Distributor/branch 1 way RMD 2-wires**

**Technical characteristics**

**Functions**

System functions branches of a stub line

**Dimensions**

Width of rail mounted device (RMD) 1 modules

**Attenuation**

Transmission loss 1 dB

**Installation, mounting**

Mounting type din-Rail

Installation mode Rail mounted unit (RMD)

**Connection**

Bus connection 2-wire, for video door stations ; 2-wire, for video indoor stations

**Cable**

Conductor Ø 0.5...0.8 mm

**Use**

System technology 2-wire

Video distribution for branching off the bus cable from the continuous bus cable ; unwired terminals must be completed with terminator

**Software**

Software version V1000

**Safety**

REACH conform Yes

RoHS conform Yes

Halogen free No

**Use conditions**

Operating temperature 5...40 °C

Storage/transport temperature -20...60 °C

Relative humidity (without condensation) 0...65 %

**Identification**

Main design line T electronics