



REE001X

LAN interface built-in for display call module

Technical characteristics

Functions

Function	ringing
System functions	LAN interface for Display-Call-Modul DCM-256 ; web or telnet configuration ; password protected access

Configuration

Configuration	set-up and configuration with DCTERM PC software ; set-up and configuration per Telnet
---------------	---

Voltage

Operating voltage	24 V DC
-------------------	---------

Materials

Colour	black
Surface appearance	matt

Use

System technology	IP
-------------------	----

Safety

REACH conform	No
RoHS conform	Yes
Halogen free	No

Use conditions

Operating temperature	-20...70 °C
Relative humidity (without condensation)	0...65 %

Identification

Main design line	Accessories
------------------	-------------