



REK621X



IP30

Indoor station Video 2wires white polar shiny with deco plate angular TOUCH

Technical characteristics

Functions

Security functions	special functions and extended menu lockable using DIP-switches ; privacy function ; video privacy function ; manual camera activation lockable
Special functions	internal call FF / FE ; manual camera and door activation/change-over ; - Parallel call to call push-button intercom device address 0
System functions	acoustic and optical call signalling via LED and display ; Storey call forwarding ; parallel operation of up to 3 indoor stations

Configuration

Configuration	device configuration via menu and 4pole DIP-switch
---------------	--

Voltage

Operating voltage over bus	24 V DC
----------------------------	---------

Electric current

Current consumption (operation)	≤ 220 mA
Current consumption (idle)	≤ 12 mA

Dimensions

Dimensions of display (W x H)	72.5 x 53.5 mm
-------------------------------	----------------

Power

Power consumption (operation)	5 W
Power consumption (standby)	≈ 0.18 W

Resistance

Terminator (terminating resistor), can be clamped	100 Ω
---	-------

Screen

Resolution graphical display	320 x 240 px
Display diagonal	88.9 mm
Display diagonal	8,9 cm (3,5")

Materials

Colour	polarwhite
Material	plastic

Installation, mounting

For surface-mounting on a flat surface or on a wall box	according to DIN 49073
Installation mode	for vertical mounting

Connection

Conductor cross-section (connection terminal block) max. 0.75 mm²

Cable

Conductor Ø 0.5...0.8 mm

Settings

Device addressing rotary coding switch (one-man commissioning)

Display languages German, English, French, Italian, Dutch

Audio settings ring tone volume and microphone sensitivity can be adjusted incrementally

Calling settings hands-free or Push-to-Talk

Equipment

Menu control 3 menu operation buttons for settings and for triggering the functions appearing in the display ; menu access and change-over by horizontal swipe movement on the touch user interface

Ring tone volume (signal) according to DIN EN 50486

Ring tone volume max. 78 dB at a distance of 0.5 m

Call volume (hands-free) max. 65 dBA

Use

Ring tone melody 16 ring tone melodies ; door call, storey call or internal call assignment ; shut-off button for ring tone, with status LED

System technology 2-wire

Use conditions

Operating temperature 5...50 °C

Storage/transport temperature -20...60 °C (storage at > 45°C reduces the service life)

Relative humidity (without condensation) 0...65 %