



REN091X



## Call push-but mod 1/1 with LED name plate and LED st ind built-in 2-wire modesta

### Technical characteristics

#### Functions

Function	ringing
----------	---------

#### Compatibility

For labelling strip	30 mm
---------------------	-------

#### Controls and indicators

Call push-button	call button can be adjusted with light, door release or without function on the audio or video module ; call push-button with acknowledge tone (can be switched off on the audio or video module) and tactile feedback
Number of call buttons	1

#### Voltage

Operating voltage	24 V DC
-------------------	---------

#### Dimensions

Depth	19 mm
Insertion depth	22.5 mm
Distance mounting dowels (horizontal/vertical)	110 mm
Dimensions front plate (W x H x D)	120 x 120 x 2 mm
Dimensions name plate (W x D)	75.5 x 32.6 mm
Dimensions name plate insert (W x H x D)	72.4 x 30.1 x 0.14 mm
Height	120 mm
Width of name plate insert	max. 0.5 mm
Width	120 mm
Material thickness stainless steel	2 mm

#### Materials

Colour of design line	Stainless steel
Colour	Stainless steel
Material / workmanship	metal brushed
Surface appearance	matt
Material / surface	stainless steel surface, brushed transversely

#### Use

System technology	2-wire
-------------------	--------

#### Use conditions

Operating temperature	-20...55 °C
-----------------------	-------------

Storage/transport temperature	-30...80 °C
Relative humidity (without condensation)	0...65 % (without condensation)