



REN092X



Call push-but mod 2/1 with LED name plate and LED st ind built-in 2-wire modesta

Technical characteristics

Functions

Function	ringing
----------	---------

Compatibility

For labelling strip	12 mm
---------------------	-------

Controls and indicators

Indication / display	with LED status display for bell, intercom connection and door release
----------------------	--

Call push-button	call button can be adjusted with light, door release or without function on the audio or video module ; call push-button with acknowledge tone (can be switched off on the audio or video module) and tactile feedback
------------------	--

Number of call buttons	2
------------------------	---

Voltage

Operating voltage	24 V DC
-------------------	---------

Dimensions

Depth	19 mm
-------	-------

Insertion depth	22.5 mm
-----------------	---------

Distance mounting dowels (horizontal/vertical)	110 mm
--	--------

Dimensions front plate (W x H x D)	120 x 120 x 2 mm
------------------------------------	------------------

Dimensions name plate (W x D)	75.5 x 14.5 mm
-------------------------------	----------------

Dimensions name plate insert (W x H x D)	72.4 x 12 x 0.14 mm
--	---------------------

Height	120 mm
--------	--------

Width of name plate insert	max. 0.5 mm
----------------------------	-------------

Width	120 mm
-------	--------

Materials

Colour of design line	Stainless steel
-----------------------	-----------------

Colour	Stainless steel
--------	-----------------

Material / workmanship	metal brushed
------------------------	---------------

Surface appearance	matt
--------------------	------

Material / surface	stainless steel surface, brushed transversely
--------------------	---

Installation, mounting

Installation mode	break-proof, flush-mounted call push-button and status display
-------------------	--

Connection

Type of connection	Connection via module connecting cable
--------------------	--

Connection	2 connections for module connecting cable
------------	---

Equipment

Lighting	durable, homogeneous, white LED call push-button backlighting ; Twilight controlled call push-button backlighting with adjustable switch-on brightness level
----------	--

Use

System technology	2-wire
-------------------	--------

Use conditions

Operating temperature	-20...55 °C
-----------------------	-------------

Storage/transport temperature	-30...80 °C
-------------------------------	-------------

Relative humidity (without condensation)	0...65 % (without condensation)
--	---------------------------------

Identification

Main design line	Modesta
------------------	---------