



REN704X



## Keyboard module for display call built-in stainless steel matt modesta

### Technical characteristics

#### Functions

Function	ringing
System functions	operation/function only in combination with DCM-256 ; access control via combination of numbers ; own code definition for each relay ; individual 1 ... 6 digit codes programmable ; own switching duration for each relay

#### Controls and indicators

Number of function keys	12
Number of call buttons	0

#### Voltage

Operating voltage	24 V DC
-------------------	---------

#### Dimensions

Depth	26 mm
Distance mounting dowels (horizontal/vertical)	110 mm
Dimensions front plate (W x H x D)	120 x 120 x 2 mm
Height	120 mm
Width	120 mm
Material thickness stainless steel	2 mm

#### Materials

Colour of design line	Stainless steel
Colour	Stainless steel
Material / workmanship	metal brushed
Surface appearance	matt
Material / surface	stainless steel surface, brushed transversely

#### Installation, mounting

Distance screw pillars (horizontal/vertical)	110/110 mm
--	------------

#### Safety

REACH conform	No
RoHS conform	Yes
Halogen free	No

#### Use conditions

Operating temperature	-20...70 °C
Relative humidity (without condensation)	0...65 %