



REN705S



Display Call Module for Modesta with German and English text

Technical characteristics

Functions

Function	ringing
	256 call destination entries each with 16 characters for the name ; 16 characters for additional information and 1...6-digit call numbers ; list of names in alphabetical order ; easy operation by means of 3 button function (up/down/call) ; display of call status and intercom connection ; dynamic search speed with long push-button action ; in idle state animated operating instructions in the display
System functions	

Configuration

Configuration	set-up with DCTERM PC software via DCI-256 ; set-up via keyboard with DLM-256 ; memory chip interchangeable with subscriber data
---------------	--

Controls and indicators

Number of function keys	3
Number of call buttons	1

Dimensions

Depth	39 mm
Dimensions of display (W x H)	63 x 44 mm
Distance mounting dowels (horizontal/vertical)	110 mm
Dimensions front plate (W x H x D)	120 x 120 x 2 mm
Height	120 mm
Width	120 mm
Material thickness stainless steel	2 mm

Materials

Colour of design line	Stainless steel
Colour	Stainless steel
Material / workmanship	metal brushed
Surface appearance	matt
Material / surface	stainless steel surface, brushed transversely

Installation, mounting

Distance screw pillars (horizontal/vertical)	110/110 mm
--	------------

Cable

Conductor Ø	0.5...0.8 mm
-------------	--------------

Equipment

Switching contact potential-free	max. 24V/1A
----------------------------------	-------------

Use

System technology	2-wire
-------------------	--------

Safety

REACH conform	No
RoHS conform	Yes
Halogen free	No

Use conditions

Operating temperature	-20...70 °C
Relative humidity (without condensation)	0...65 %