



REQ016X



IK07 IP54

Door station AUDIO 16/2 2-wire stainless steel matt one

Technical characteristics

Architecture

Fixing mode flush-mounting or surface-mounting

Functions

Security functions privacy function

Compatibility

For labelling strip 12 mm

Controls and indicators

Call push-button call button can be adjusted with light, door release or without function ; call push-button with acknowledge tone (can be switched off) and tactile feedback

Call push-button closing time max. 3 s

Number of call buttons 16

Operating functions door release during connection or at any time adjustable

Voltage

Switching voltage door release contact max. 24 V

Electric current

Switching current door release contact max. 1 A

Dimensions

Depth 25 mm

Insertion depth 22.5 mm

Surface adjustment 17 mm

Dimensions front plate (W x H x D) 225.5 x 332 x 2 mm

Dimensions name plate insert (W x H) 72.4 x 12 mm

Dimensions name plate insert (W x H x D) 72.4 x 12 x 0.14 mm

Height 332 mm

Width of name plate insert max. 0.5 mm

Width 225.5 mm

Material thickness stainless steel 2 mm

Materials

Colour of design line Stainless steel

Colour Stainless steel

Material stainless steel

Surface appearance matt

LED control

Operating voltage LED	12 V AC
-----------------------	---------

LED operating current per call push-button module	45 mA
---	-------

Installation, mounting

Installation mode	for vertical mounting
-------------------	-----------------------

Cable

Conductor Ø	0.5...1.4 mm
-------------	--------------

Accessories included

Tool	with opening tool
------	-------------------

Equipment

Door release unlocking time	1...10 s
-----------------------------	----------

Front plate	front plate with non-visible opening mechanics and safety rope
-------------	--

Use

System technology	2-wire
-------------------	--------

Use conditions

Operating temperature	-20...55 °C
-----------------------	-------------

Storage/transport temperature	-30...80 °C
-------------------------------	-------------

Relative humidity (without condensation)	0...65 % (without condensation)
--	---------------------------------

Instructions

Information text	Caution! Do not aim the camera at direct light sources / sunlight, strong contrast or a highly reflective background.
------------------	---
