



RLA144X

pet-tolerant anti-masking external movement detector

Technical characteristics

Connectivity

Connection mode radio TwinBand

Voltage

Operating voltage 3600 mV

Electric current

Current consumption (operation) 28 mA

Dimensions

Dimensions (LLxwxh) 71X106X186

Measurement

Detection Method Passive Infrared

Detection

Range of detection 12 m

Equipment

Angle of horizontal detection 90 °

Use

Lense type Pet-tolerant

Standards

European directive WEEE concerned

Safety

Protection index IP IP55

Use conditions

Operating temperature -20...60 °C