



S155-22X

Smoke detector, radio, 10 year-lithium battery

Technical characteristics

Architecture

Fixing mode	Screwed
-------------	---------

Functions

Operating type	System
Built-in sounder	Yes, 85 dB at 3 m
Smoke switcher	No

Connectivity

Standard network connexion by cable	No
Optional interconnection by radio	No
Standard interconnection by radio	Yes
Networkable	Yes

Voltage

Input voltage	≈ 6 V
---------------	-------

Dimensions

Dimensions (LLxwwxhh)	116x49 mm
-----------------------	-----------

Network voltage

With voltage indication	No
-------------------------	----

Measurement

Detection Range	50 m ²
Detection Method	Optical

Battery

life of battery	10 years lithium battery no replacaeble
Weak battery warning	Yes

Scope of delivery

Rechargeable battery backup included	No
Type of battery backup included	none

Equipment

Number of connexions for sensors / actuator	40
Standalone	No
VDS accepted	No
Sounder volume	85 dB

Standards

Q-Label certification	No
European directive WEEE	concerned

Safety

Protection index IP	IP22
---------------------	------

Use conditions

Operating temperature	-10...65 °C
-----------------------	-------------
