



S165-22X

Expert pet tolerant motion detector, 85°, 12 meters

Technical characteristics

Connectivity

Connection mode radio TwinBand

Voltage

Operating voltage 3 V

Dimensions

Dimensions (LLxwwxhh) 58 x 102 x 57 mm

Measurement

Detection Method Passive Infrared

Detection

Range of detection 12 m

Equipment

Angle of horizontal detection 85 °

Use

Lense type Pet-tolerant

Standards

European directive WEEE concerned

Use conditions

Operating temperature -10...40 °C

temperatur

Ambient temperature 10...40 °C