


SK600



## Selector switch non spring ret

### Technical characteristics

#### Architecture

Number of poles 1 P

#### Configuration

Number of modules 3

#### Controls and indicators

Number of positions of the switch 3

#### Main electrical features

Rated operational voltage  $U_e$  400 V

Frequency 50 Hz

#### Voltage

Rated insulation voltage 690 V

#### Electric current

Rated current 20 A

#### Dimensions

Depth of installed product 64 mm

Height of installed product 85 mm

Width of installed product 53 mm

#### Power

Total power loss under IN 0.7 W

#### Connection

Connection cross-sect. flexible conductor 1,5 / 10mm<sup>2</sup>

Connection cross-sect. rigid cable 1 / 6mm<sup>2</sup>

Number of contacts 1

Type of contacts NO-NC

Type of connection with screw

#### Safety

REACH conform Yes

RoHS conform Yes

Halogen free Yes

#### Use conditions

Operating temperature -10...40 °C

