



SK602



Voltmeter switch 3"o

Technical characteristics

Architecture

Fixing mode Din-Rail

Configuration

Number of modules 3

Controls and indicators

Number of positions of the switch 7

Main electrical features

Frequency 50 Hz

Voltage

Rated insulation voltage 690 V

Electric current

Rated current 20 A

Dimensions

Depth of installed product 64 mm

Height of installed product 85 mm

Width of installed product 70 mm

Power

Total power loss under IN 1 W

Network configuration

Network type tree-phase with neutral

Installation, mounting

Mounting type din-Rail

Safety

Protection index IP IP20

Use conditions

Operating temperature -10...40 °C

Storage/transport temperature -40...80 °C