



SK602



## Voltmeter switch 3"o

### Technical characteristics

#### Configuration

Number of modules 3

#### Controls and indicators

Number of positions of the switch 7

#### Main electrical features

Frequency 50 Hz

#### Voltage

Rated insulation voltage 690 V

#### Electric current

Rated current 20 A

#### Dimensions

Depth of installed product 64 mm

Height of installed product 85 mm

Width of installed product 70 mm

#### Power

Total power loss under IN 1 W

#### Network configuration

Network type tree-phase with neutral

#### Installation, mounting

Mounting type din-Rail

#### Connection

Connection cross-sect. flexible conductor 1,5 / 10mm<sup>2</sup>

Connection cross-sect. rigid cable 1 / 6mm<sup>2</sup>

Type of connection with screw

#### Safety

REACH conform Yes

RoHS conform Yes

Halogen free Yes

#### Use conditions

Operating temperature -10...40 °C

Storage/transport temperature -40...80 °C