



SK602



**Voltmeter switch 3"o**

**Technical characteristics**

**Configuration**

Number of modules 3

**Controls and indicators**

Number of positions of the switch 7

**Main electrical features**

Frequency 50 Hz

**Voltage**

Rated insulation voltage 690 V

**Electric current**

Rated current 20 A

**Dimensions**

Depth of installed product 64 mm

Height of installed product 85 mm

Width of installed product 70 mm

**Power**

Total power loss under IN 1 W

**Network configuration**

Network type tree-phase with neutral

**Installation, mounting**

Mounting type din-Rail

**Connection**

Connection cross-sect. flexible conductor 1,5 / 10mm<sup>2</sup>

Connection cross-sect. rigid cable 1 / 6mm<sup>2</sup>

Type of connection with screw

**Safety**

REACH conform Yes

RoHS conform Yes

Halogen free Yes

**Use conditions**

Operating temperature -10...40 °C

Storage/transport temperature -40...80 °C