




SL2008039011



External corner VDI for trunking tehalit.SL 20x80mm graphite black

Technical characteristics

Architecture

Fixing mode Clamping

Dimensions

Trunking height 80 mm

Trunking width 20 mm

Cover, door

Lid with softlip No

Materials

Colour graphite black

RAL colour RAL 9011 - Graphite black

Material ABS

Material group plastic

Type of surface treatment untreated

Settings

Angle range 83 / 135 °

Accessories included

Accessory configuration Moulded

Standards

Approvals CE

European directive RoHS voluntary compliance

Safety

Protection index IP IP40

Impact strength IK07

Use conditions

Operating temperature 5...60 °C

temperatur

Ambient temperature 5...60 °C