




SL200804D1



Internal corner VDI for trunking tehalit.SL 20x80mm alu

Technical characteristics

Architecture

Fixing mode	Clamping
-------------	----------

Dimensions

Trunking height	80 mm
Trunking width	20 mm

Cover, door

Lid with softlip	No
------------------	----

Materials

Material group	plastic
----------------	---------

Settings

Angle range	83 / 135 °
-------------	------------

Accessories included

Accessory configuration	Moulded
-------------------------	---------

Standards

Approvals	CE
European directive RoHs	voluntary compliance

Safety

REACH conform	Yes
RoHS conform	Yes
Impact strength	IK07

Use conditions

Operating temperature	5...60 °C
-----------------------	-----------

temperatur

Ambient temperature	5...60 °C
---------------------	-----------