



SL2008079011



Joint cover for trunking tehalit.SL 20x80mm graphite black

Technical characteristics

Architecture

Fixing mode	Clamping
-------------	----------

Dimensions

Trunking height	80 mm
Trunking width	20 mm

Materials

Material group	plastic
Type of surface treatment	untreated

Standards

Approvals	CE
European directive RoHS	voluntary compliance

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Impact strength	IK07

Use conditions

Operating temperature	5...60 °C
-----------------------	-----------

temperatur

Ambient temperature	5...60 °C
---------------------	-----------