




SL2011539010



External corner VDI for trunking tehalit.SL 20x115mm pure white

Technical characteristics

Architecture

Fixing mode Clamping

Dimensions

Trunking height 115 mm

Trunking width 20 mm

Cover, door

Lid with softlip No

Materials

RAL colour RAL 9010 - Pure white

Material group plastic

Type of surface treatment untreated

Settings

Angle range 83 / 135 °

Accessories included

Accessory configuration Moulded

Standards

European directive RoHs voluntary compliance

Safety

Impact strength IK07

Use conditions

Operating temperature 5...60 °C

temperatur

Ambient temperature 5...60 °C