



SM401

Digital ammeter 0-400A indirect reading

Technical characteristics

Functions

Precision class	1%
-----------------	----

Configuration

Number of modules	4
-------------------	---

Controls and indicators

Measurement scale	400 A
-------------------	-------

Main electrical features

Rated operational voltage Ue	207 / 230 / 253 V
------------------------------	-------------------

Frequency	45/65 Hz
-----------	----------

Voltage

Voltage drop	120 mV
--------------	--------

Dimensions

Depth of installed product	54 mm
----------------------------	-------

Height of installed product	85 mm
-----------------------------	-------

Width of installed product	70 mm
----------------------------	-------

Power

Power consumed	1 VA
----------------	------

Total power loss under IN	1 W
---------------------------	-----

Installation, mounting

Modular version	Yes
-----------------	-----

Mounting type	din-Rail
---------------	----------

Connection

Connection cross-sect. flexible conductor	6mm ²
---	------------------

Connection cross-sect. rigid cable	10mm ²
------------------------------------	-------------------

Equipment

Digits number	3
---------------	---

Safety

RoHS conform	Yes
--------------	-----

Use conditions

Operating temperature	-10...55 °C
-----------------------	-------------

Storage/transport temperature	-40...70 °C
-------------------------------	-------------