



SM501

## Digital voltmeter

### Technical characteristics

#### Functions

Precision class	1%
-----------------	----

#### Configuration

Number of modules	4
-------------------	---

#### Main electrical features

Rated operational voltage Ue	230 V
Frequency	45/65 Hz

#### Dimensions

Depth of installed product	54 mm
Height of installed product	90 mm
Width of installed product	70 mm

#### Power

Power consumed	3.5 VA
Total power loss under IN	3.5 W

#### Measurement

Voltage measurement range	0 to 500 V
Type of measuring instrument	voltmeter

#### Installation, mounting

Mounting type	din-Rail
---------------	----------

#### Connection

Connection cross-sect. flexible conductor	6mm <sup>2</sup>
Connection cross-sect. rigid cable	10mm <sup>2</sup>
Type of connection	with screw

#### Equipment

Digits number	3
---------------	---

#### Safety

REACH conform	Yes
RoHS conform	Yes

#### Use conditions

Operating temperature	-10...55 °C
Storage/transport temperature	-40...70 °C